

**ZBWW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Our special tools support within the cabinet process in the area of wiring or also the assembly of the components.

**General ordering data**

Version	Z-series, Operating tool
Order No.	<a href="#">1669630000</a>
Type	ZBWW
GTIN (EAN)	4008190429119
Qty.	1 pc(s).

**ZBWW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	23.75 mm	Depth (inches)	0.935 inch
Height	140.18 mm	Height (inches)	5.519 inch
Width	27.76 mm	Width (inches)	1.093 inch
Net weight	17.439 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-40
Continuous operating temp., max.	100		

**Material data**

Material	POM	Colour	orange
UL 94 flammability rating	HB		

**System specifications**

Version	Operating tool
---------	----------------

**Additional technical data**

Explosion-tested version	No
--------------------------	----

**Classifications**

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>