

HDC-CM-5BCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The ConCept system features flexible and all-purpose modules. Depending on the application, you can choose from a wide variety of modules based on your requirements. The modules differ according to electrical specifications and their respective wire connection methods. Any number of combinations can be created with the ever-growing number of modules.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1682110000
Type	HDC-CM-5BCM
GTIN (EAN)	4008190473846
Qty.	10 pc(s).

HDC-CM-5BCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	34 mm	Length (inches)	1.339 inch
Net weight	9.5 g		

ConCept Pneumatic module

Colour	black	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

Dimensions

Height of socket	11.4 mm	Total length base	34 mm
------------------	---------	-------------------	-------

General data

Colour	black	Free from halogens	false
Insulation strength	10 ¹¹ Ω	Low smoke acc. DIN EN 45545-2	Yes
Number of poles	5	Pollution severity	3
Rated current (DIN EN 61984)	20 A	Rated impulse voltage (DIN EN 61984)	6 kV
Rated voltage (DIN EN 61984)	400 V	Series	ConCept module
Surge voltage category	III	Type	Female
UL 94 flammability rating	V-0	Volume resistance	5.00 mΩ

Connection data PE

Connection type PE	Crimp connection
--------------------	------------------

Version

Conductor cross-section, max.	4 mm ²	Conductor cross-section, min.	0.75 mm ²
Volume resistance	5.00 mΩ	Wire connection cross section AWG, max.	AWG 12

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

HDC-CM-5BCM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimp contacts CM5



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC-C-M5-BM2.5AG	Version
Order No.	1682390000	Heavy-duty connectors, Crimp contact, CM 5, Female, Conductor
GTIN (EAN)	4008190474126	cross-section, max.: 2.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-BM4.0AG	Version
Order No.	1682410000	Heavy-duty connectors, Crimp contact, CM 5, Female, Conductor
GTIN (EAN)	4008190474140	cross-section, max.: 4, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-SM1.5AG	Version
Order No.	1682360000	Heavy-duty connectors, Crimp contact, CM 5, Pin, Conductor cross-
GTIN (EAN)	4008190474096	section, max.: 1.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-SM2.5AG	Version
Order No.	1682380000	Heavy-duty connectors, Crimp contact, CM 5, Pin, Conductor cross-
GTIN (EAN)	4008190474119	section, max.: 2.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-SM4.0AG	Version
Order No.	1682400000	Heavy-duty connectors, Crimp contact, CM 5, Pin, Conductor cross-
GTIN (EAN)	4008190474133	section, max.: 4, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-BM0.75-1.0AG	Version
Order No.	1682350000	Heavy-duty connectors, Crimp contact, CM 5, Female, Conductor
GTIN (EAN)	4008190474089	cross-section, max.: 1, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-BM0.5AG	Version
Order No.	1682330000	Heavy-duty connectors, Crimp contact, CM 5, Female, Conductor
GTIN (EAN)	4008190474065	cross-section, max.: 0.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-SM0.75-1.0AG	Version
Order No.	1682340000	Heavy-duty connectors, Crimp contact, CM 5, Pin, Conductor cross-
GTIN (EAN)	4008190474072	section, max.: 1, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M5-SM0.5AG	Version
Order No.	1682320000	Heavy-duty connectors, Crimp contact, CM 5, Pin, Conductor cross-
GTIN (EAN)	4008190474058	section, max.: 0.5, turned, Copper alloy
Qty.	100 pc(s).	

HDC-CM-5BCM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	HDC-C-M5-BM1.5AG	Version
Order No.	1682370000	Heavy-duty connectors, Crimp contact, CM 5, Female, Conductor
GTIN (EAN)	4008190474102	cross-section, max.: 1.5, turned, Copper alloy
Qty.	100 pc(s).	

Modul removal tool

Weidmüller offers a variety of crimping tools, no-contact tools, and fibre optic tools.

General ordering data

Type	HDC-DW-M0D	Version
Order No.	1688200000	Tool miscellaneous, Contact Removal Tool
GTIN (EAN)	4008190857189	
Qty.	1 pc(s).	