

**QL 3 SAKG54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 3, Pitch in mm (P): 54.00, Insulated: No, 415 A, grey
Order No.	<a href="#">0408000000</a>
Type	QL 3 SAKG54
GTIN (EAN)	4008190069711
Qty.	5 pc(s).

**QL 3 SAKG54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	6 mm	Depth (inches)	0.236 inch
Height	17 mm	Height (inches)	0.669 inch
Width	148 mm	Width (inches)	5.827 inch
Net weight	281.6 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	CuSn	Colour	grey
----------	------	--------	------

**System specifications**

Version	Cross-connector
---------	-----------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	415 A
Rated current, multi-pole	415 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	54 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	415 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--