

VH 10/4/2.8 AKZ4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

Version	Connecting sleeve (terminal), Height: 4 mm, Width: 4 mm, Depth: 10 mm, Cu Zn
Order No.	0446600000
Type	VH 10/4/2.8 AKZ4
GTIN (EAN)	4008190176211
Qty.	50 pc(s).
Delivery status	Discontinued
Available until	2020-06-04

VH 10/4/2.8 AKZ4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	10 mm	Depth (inches)	0.394 inch
Height	4 mm	Height (inches)	0.157 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.56 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	1	Type	Cross-connector
-------------------------------------	---	------	-----------------

General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format