

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Product image**







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

### **General ordering data**

| Version             | SAK Series, Feed-through terminal, Rated cross-<br>section: 6 mm², Screw connection, medium yel-<br>low, Direct mounting |
|---------------------|--------------------------------------------------------------------------------------------------------------------------|
| Order No.           | <u>0550420000</u>                                                                                                        |
| Туре                | SAKT 1/DU2                                                                                                               |
| GTIN (EAN)          | 4008190140373                                                                                                            |
| Qty.                | 50 pc(s).                                                                                                                |
| Delivery status     | Discontinued                                                                                                             |
| Available until     | 2022-12-31                                                                                                               |
| Alternative product | 2710090000                                                                                                               |

Creation date March 29, 2024 11:42:28 AM CET



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

| -   | -       |     |         |
|-----|---------|-----|---------|
| Dım | ensions | and | weights |
|     |         |     |         |

| Depth      | 52.5 mm | Depth (inches)  | 2.067 inch |
|------------|---------|-----------------|------------|
| Height     | 65 mm   | Height (inches) | 2.559 inch |
| Width      | 8 mm    | Width (inches)  | 0.315 inch |
| Net weight | 23.56 g |                 |            |

### **Temperatures**

| Storage temperature              | -25 °C55 °C | Continuous operating temp., min. | -60 °C |  |
|----------------------------------|-------------|----------------------------------|--------|--|
| Continuous operating temp., max. | 130 °C      |                                  |        |  |

### **Material data**

| Material                  | KrG      | Colour | medium yellow |
|---------------------------|----------|--------|---------------|
| UL 94 flammability rating | V-0, 5VA |        |               |

### **System specifications**

| Version                             | Screw connection, for screwable cross-connection, in | End cover plate required      |     |
|-------------------------------------|------------------------------------------------------|-------------------------------|-----|
|                                     | closed state                                         |                               | Yes |
| Number of potentials                | 1                                                    | Number of levels              | 1   |
| Number of clamping points per level | 2                                                    | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No                                                   | PE connection                 | No  |
| Rail                                | TS 32                                                | N-function                    | No  |
| PE function                         | No                                                   | PEN function                  | No  |

### **Additional technical data**

| Explosion-tested version    | No      | Installation advice | Direct mounting |
|-----------------------------|---------|---------------------|-----------------|
| Number of similar terminals | 1       | Open sides          | right           |
| Type of mounting            | Snap-on |                     |                 |

### **Conductors for clamping (rated connection)**

| Blade size                                                                              | 4.0 x 0.8 mm         | Clamping range, max.                                                                            | 10 mm <sup>2</sup>  |
|-----------------------------------------------------------------------------------------|----------------------|-------------------------------------------------------------------------------------------------|---------------------|
| Clamping range, min.                                                                    | 0.13 mm <sup>2</sup> | Clamping screw                                                                                  | M 3.5               |
| Connection cross-section, stranded,                                                     |                      | Connection cross-section, stranded, min                                                         | n.                  |
| max.                                                                                    | 10 mm <sup>2</sup>   |                                                                                                 | 1.5 mm <sup>2</sup> |
| Connection direction                                                                    | on side              | Gauge to IEC 60947-1                                                                            | A5                  |
| Number of connections                                                                   | 2                    | Stripping length                                                                                | 12 mm               |
| Tightening torque, max.                                                                 | 1.6 Nm               | Tightening torque, min.                                                                         | 0.8 Nm              |
| Torque level with DMS electric screw-<br>driver                                         | 3                    | Type of connection                                                                              | Screw connection    |
| Wire connection cross section AWG, max.                                                 | AWG 8                | Wire connection cross section AWG, min.                                                         | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 6 mm²                | Wire connection cross section, finely stranded, min.                                            | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm²                | Wire connection cross-section, fine-<br>ly stranded with wire-end ferrules DIN<br>46228/1, min. | 0.5 mm²             |
| Wire connection cross-section, solid core, max.                                         | 10 mm²               | Wire connection cross-section, solid core, min.                                                 | 0.5 mm <sup>2</sup> |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

#### General

| Installation advice           | Direct mounting | Rail                  | TS 32        |
|-------------------------------|-----------------|-----------------------|--------------|
| Standards                     |                 | Wire connection cross | section AWG, |
|                               | IEC 60947-7-1   | max.                  | AWG 8        |
| Wire connection cross section | AWG,            |                       |              |
| min                           | Δ\MG 26         |                       |              |

### **Rating data**

| Rated cross-section                | 6 mm <sup>2</sup>     | Rated voltage               | 400 V         |
|------------------------------------|-----------------------|-----------------------------|---------------|
| Rated DC voltage                   | 400 V                 | Rated current               | 41 A          |
| Current at maximum wires           | 57 A                  | Standards                   | IEC 60947-7-1 |
| Volume resistance according to IEC | C                     | Rated impulse withstand vol | tage          |
| 60947-7-x                          | $0.78~\text{m}\Omega$ |                             | 6 kV          |
| Power loss in accordance with IEC  |                       | Pollution severity          |               |
| 60947-7-x                          | 1.31 W                |                             | 3             |

#### Classifications

| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ECLASS 9.0  | 27-14-11-20 | ECLASS 9.1  | 27-14-11-20 |
| ECLASS 10.0 | 27-14-11-20 | ECLASS 11.0 | 27-14-11-20 |
| ECLASS 12.0 | 27-14-11-20 | ECLASS 13.0 | 27-25-01-01 |

## **Approvals**

Approvals



| ROHS Conform |
|--------------|
|--------------|

#### **Downloads**

| Approval/Certificate/Document of Con- |                                        |
|---------------------------------------|----------------------------------------|
| formity                               | Declaration of Conformity              |
| Engineering Data                      | CAD data – STEP                        |
| User Documentation                    | <u>StorageConditionsTerminalBlocks</u> |
| Catalogues                            | Catalogues in PDF-format               |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **SAK-Series**



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

### **General ordering data**

| Туре              | TW SAKB/C/T1                  | Version                                                                  |
|-------------------|-------------------------------|--------------------------------------------------------------------------|
| Order No.         | 0242960000                    | SAK Series, Partition plate, 1.5 mm, beige, Direct mounting              |
| GTIN (EAN)        | 4008190104092                 |                                                                          |
| Qty.              | 20 pc(s).                     |                                                                          |
|                   |                               |                                                                          |
| Туре              | AP SAKB/C/T KRG               | Version                                                                  |
| Type<br>Order No. | AP SAKB/C/T KRG<br>0146720000 | Version SAK Series, End plate, 3 mm, dark beige, yellow, Direct mounting |
|                   | , ,                           |                                                                          |

### **Fixing screws**



Fixing screws fix the short current bridge within the application. If the short current bridge is slided between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

## **General ordering data**

| Туре                            | BS 25 IH/GE SAKT1                                             | Version                             |
|---------------------------------|---------------------------------------------------------------|-------------------------------------|
| Order No.                       | 0335700000                                                    | SAK Series, Set of fixings          |
| GTIN (EAN)                      | 4008190189235                                                 |                                     |
| Qty.                            | 50 pc(s).                                                     |                                     |
| Туре                            | KISC M3X20 SAK10 CU5                                          | Version                             |
| Order No.                       | 0377100000                                                    | SAK Series, Mounting screw, Copper  |
| GTIN (EAN)                      | 4008190060350                                                 |                                     |
| Qty.                            | 100 pc(s).                                                    |                                     |
|                                 |                                                               |                                     |
| Туре                            | BS 25 IH/GR SAKT1                                             | Version                             |
| Type<br>Order No.               | BS 25 IH/GR SAKT1<br>0335300000                               | Version SAK Series, Set of fixings  |
|                                 |                                                               |                                     |
| Order No.                       | 0335300000                                                    |                                     |
| Order No.<br>GTIN (EAN)         | <u>0335300000</u><br>4008190136864                            |                                     |
| Order No.<br>GTIN (EAN)<br>Qty. | 0335300000<br>4008190136864<br>50 pc(s).                      | SAK Series, Set of fixings          |
| Order No. GTIN (EAN) Oty. Type  | 0335300000<br>4008190136864<br>50 pc(s).<br>BS 25 IH/RT SAKT1 | SAK Series, Set of fixings  Version |

Creation date March 29, 2024 11:42:28 AM CET



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

| Туре       | BS 25 IH/SW SAKT1 | Version                    |
|------------|-------------------|----------------------------|
| Order No.  | 0335200000        | SAK Series, Set of fixings |
| GTIN (EAN) | 4008190114039     |                            |
| Qty.       | 50 pc(s).         |                            |

#### **Z-Series**

Z Series Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### **General ordering data**

| Туре              | ZEW 35/2             | Version                       |
|-------------------|----------------------|-------------------------------|
| Order No.         | <u>8630740000</u>    | Z-series, End bracket         |
| GTIN (EAN)        | 4032248348916        |                               |
| Qty.              | 20 pc(s).            |                               |
|                   |                      |                               |
| Туре              | ZEW 35               | Version                       |
| Type<br>Order No. | ZEW 35<br>9540000000 | Version Z-series, End bracket |
|                   |                      |                               |

#### **Test sockets**



The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

### **General ordering data**

| Туре       | STB 21.6/IH/GN WTL6/3 | Version             |
|------------|-----------------------|---------------------|
| Order No.  | <u>1071020000</u>     | Accessories, Socket |
| GTIN (EAN) | 4008190259228         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 36.8/IH/DB WTL6/1 | Version             |
| Order No.  | <u>1847740000</u>     | Accessories, Socket |
| GTIN (EAN) | 4032248379187         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/VI WTL6/3 | Version             |
| Order No.  | 1071030000            | Accessories, Socket |
| GTIN (EAN) | 4008190259235         |                     |
| Qty.       | 50 pc(s).             |                     |

Creation date March 29, 2024 11:42:28 AM CET



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

| Туре       | STB 36.8/IH/BL WTL6/1 | Version             |
|------------|-----------------------|---------------------|
| Order No.  | <u>1847790000</u>     | Accessories, Socket |
| GTIN (EAN) | 4032248379149         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/DB WTL6/3 | Version             |
| Order No.  | 1071000000            | Accessories, Socket |
| GTIN (EAN) | 4008190259204         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 36.8/IH/GN WTL6/1 | Version             |
| Order No.  | 1847770000            | Accessories, Socket |
| GTIN (EAN) | 4032248379163         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/BL WTL6/3 | Version             |
| Order No.  | 1071080000            | Accessories, Socket |
| GTIN (EAN) | 4008190043957         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/SW WTL6/3 | Version             |
| Order No.  | 1071040000            | Accessories, Socket |
| GTIN (EAN) | 4008190859985         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 36.8/IH/VI WTL6/1 | Version             |
| Order No.  | <u>1847780000</u>     | Accessories, Socket |
| GTIN (EAN) | 4032248379156         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 36.8/IH/GE WTL6/1 | Version             |
| Order No.  | 1847760000            | Accessories, Socket |
| GTIN (EAN) | 4032248379170         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/RT WTL6/3 | Version             |
| Order No.  | <u>1778990000</u>     | Accessories, Socket |
| GTIN (EAN) | 4032248169665         |                     |
| Qty.       | 50 pc(s).             |                     |
| Туре       | STB 21.6/IH/GE WTL6/3 | Version             |
| Order No.  | <u>1071010000</u>     | Accessories, Socket |
| GTIN (EAN) | 4008190259211         |                     |
| Qty.       | 50 pc(s).             |                     |
|            |                       |                     |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

### **Test plugs**



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### **General ordering data**

Type PS 4 F.STB 4
Order No. 0299600000
GTIN (EAN) 4008190074043
Oty. 20 pc(s).

. . .

Accessories, Test plug

### **Shorting elements**



The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

| Туре                            | QVS 3 SAKT1+2                                            | Version                                                                   |
|---------------------------------|----------------------------------------------------------|---------------------------------------------------------------------------|
| Order No.                       | 0329300000                                               | SAK Series, Cross-connector, Cross-connector, Number of poles: 3          |
| GTIN (EAN)                      | 4008190084714                                            |                                                                           |
| Qty.                            | 20 pc(s).                                                |                                                                           |
| Туре                            | QVS 2 SAKT1+2                                            | Version                                                                   |
| Order No.                       | 0307300000                                               | SAK Series, Cross-connector, Cross-connector, Number of poles: 2          |
| GTIN (EAN)                      | 4008190036140                                            |                                                                           |
| Qty.                            | 20 pc(s).                                                |                                                                           |
|                                 |                                                          |                                                                           |
| Туре                            | QVS 2/S SAKT1+2                                          | Version                                                                   |
| Type<br>Order No.               | OVS 2/S SAKT1+2<br>0358460000                            | Version SAK Series, Cross-connector, Cross-connector, Number of poles: 2  |
|                                 | · ·                                                      |                                                                           |
| Order No.                       | 0358460000                                               |                                                                           |
| Order No.<br>GTIN (EAN)         | <u>0358460000</u><br>4008190157937                       |                                                                           |
| Order No.<br>GTIN (EAN)<br>Oty. | 0358460000<br>4008190157937<br>20 pc(s).                 | SAK Series, Cross-connector, Cross-connector, Number of poles: 2          |
| Order No. GTIN (EAN) Oty. Type  | 0358460000<br>4008190157937<br>20 pc(s).<br>QVSK 2 SAKT1 | SAK Series, Cross-connector, Cross-connector, Number of poles: 2  Version |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

### **Custom printing**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type DEK 5/6.5 MC SDR

Order No. 1609850000

GTIN (EAN) 4008190456610

Oty. 180 pc(s).

Version

Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50

Weidmueller, To customer specification

### W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### General ordering data

Туре WEW 35/2 Version 1061200000 Order No. W-Series, End bracket GTIN (EAN) 4008190030230 Qty. 50 pc(s). Туре WEW 35/1 Version Order No. 1059000000 W-Series, End bracket GTIN (EAN) 4008190172282 50 pc(s). Qtv.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

## **SAK-Series**



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

### **General ordering data**

| Туре       | EW 35 GR 7032 | Version                  |
|------------|---------------|--------------------------|
| Order No.  | 0383530000    | Accessories, End bracket |
| GTIN (EAN) | 4008190027322 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | EW 35         | Version                  |
| Order No.  | 0383560000    | Accessories, End bracket |
| GTIN (EAN) | 4008190181314 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | EW 35/SCHA/M3 | Version                  |
| Order No.  | 0258660000    | Accessories, End bracket |
| GTIN (EAN) | 4008190033477 |                          |
| Qty.       | 20 pc(s).     |                          |

### QL / SAK 6N



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

| Туре       | QL 15 SAK6N   | Version                                                           |
|------------|---------------|-------------------------------------------------------------------|
| Order No.  | 0221200000    | SAK Series, Cross-connector, Cross-connector, Number of poles: 15 |
| GTIN (EAN) | 4008190042110 |                                                                   |
| Qty.       | 10 pc(s).     |                                                                   |
| Туре       | QL 4 SAK6N    | Version                                                           |
| Order No.  | 0194500000    | SAK Series, Cross-connector, Cross-connector, Number of poles: 4  |
| GTIN (EAN) | 4008190025601 |                                                                   |
| Qty.       | 50 pc(s).     |                                                                   |
| Туре       | QL 3 SAK6N    | Version                                                           |
| Order No.  | 0194400000    | SAK Series, Cross-connector, for cross-connection link, Number of |
| GTIN (EAN) | 4008190063351 | poles: 3                                                          |
| Qty.       | 50 pc(s).     |                                                                   |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

| Туре              | QL 2 SAK6N                | Version                                                                   |
|-------------------|---------------------------|---------------------------------------------------------------------------|
| Order No.         | 0194300000                | SAK Series, Cross-connector, for cross-connection link, Number of         |
| GTIN (EAN)        | 4008190182854             | poles: 2                                                                  |
| Qty.              | 50 pc(s).                 |                                                                           |
|                   |                           |                                                                           |
| Туре              | QL 10 SAK6N               | Version                                                                   |
| Type<br>Order No. | QL 10 SAK6N<br>0338300000 | Version SAK Series, Cross-connector, for cross-connection link, Number of |
|                   |                           |                                                                           |

#### **TS 32**

**TS 32** 

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

| Туре       | EWK 1         | Version                  |
|------------|---------------|--------------------------|
| Order No.  | 0206160000    | Accessories, End bracket |
| GTIN (EAN) | 4008190080020 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | EWK 1 ALT     | Version                  |
| Order No.  | 0495160000    | Accessories, End bracket |
| GTIN (EAN) | 4008190160777 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | WEW 32/1      | Version                  |
| Order No.  | 1067600000    | W-Series, End bracket    |
| GTIN (EAN) | 4008190099657 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | EWK 2         | Version                  |
| Order No.  | 0199360000    | Accessories, End bracket |
| GTIN (EAN) | 4008190023546 |                          |
| Qty.       | 50 pc(s).     |                          |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

### **End plate**



### **Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

### **General ordering data**

| Туре       | TW SAKB/C/T   | Version                                                   |
|------------|---------------|-----------------------------------------------------------|
| Order No.  | 0242920000    | SAK Series, Partition plate, 3 mm, beige, Direct mounting |
| GTIN (EAN) | 4008190069933 |                                                           |
| Qty.       | 20 pc(s).     |                                                           |

#### **Connection sleeves**



| Type              | VH 12/4.9/3.3               | Version                                                                     |
|-------------------|-----------------------------|-----------------------------------------------------------------------------|
| Order No.         | 0249000000                  | SAK Series, Connecting sleeve, for cross-connection link, Number of         |
| GTIN (EAN)        | 4008190129507               | poles:                                                                      |
| Qty.              | 100 pc(s).                  |                                                                             |
|                   |                             |                                                                             |
| Туре              | VH 19/6.3/4.3               | Version                                                                     |
| Type<br>Order No. | VH 19/6.3/4.3<br>0318000000 | Version SAK Series, Connecting sleeve, for cross-connection link, Number of |
|                   | , ,                         |                                                                             |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Accessories**

#### **Blank**



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Type DEK 5/6.5 MC NE WS
Order No. 1609840000
GTIN (EAN) 4008190203429

900 pc(s).

Version

Dekafix, Terminal marker, 5 x 6.5 mm, Pitch in mm (P): 6.50

Weidmueller, white

### Marker holder

Qty.



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon<sup>®</sup> Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

| Туре              | BZT 1 WS 10/5                  | Version                            |
|-------------------|--------------------------------|------------------------------------|
| Order No.         | 1805490000                     | Accessories, Marker holder         |
| GTIN (EAN)        | 4032248270231                  |                                    |
| Qty.              | 100 pc(s).                     |                                    |
|                   |                                |                                    |
| Туре              | BZT 1 ZA WS 10/5               | Version                            |
| Type<br>Order No. | BZT 1 ZA WS 10/5<br>1805520000 | Version Accessories, Marker holder |
|                   | ,                              |                                    |



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## Accessories

## **TS 15**

TS 15

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

| Туре       | EW 15         | Version                  |
|------------|---------------|--------------------------|
| Order No.  | 0382860000    | Accessories, End bracket |
| GTIN (EAN) | 4008190187804 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | EW 15/2       | Version                  |
| Order No.  | 1071900000    | Accessories, End bracket |
| GTIN (EAN) | 4008190462949 |                          |
| Qty.       | 50 pc(s).     |                          |
| Туре       | ZEW 15        | Version                  |
| Order No.  | 7920340000    | Accessories, End bracket |
| GTIN (EAN) | 4032248238910 |                          |
| Qty.       | 20 pc(s).     |                          |