

**MB M5/M3 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

**General ordering data**

Version	Sliding nut, M 5
Order No.	<a href="#">0553400000</a>
Type	MB M5/M3 SW
GTIN (EAN)	4008190122263
Qty.	20 pc(s).

**MB M5/M3 SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	14 mm	Depth (inches)	0.551 inch
Height	25 mm	Height (inches)	0.984 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	3.5 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Polyamide 66	Surface finish	untreated
Colour	black	UL 94 flammability rating	V-2

**System specifications**

Version	For the mounting rails	Rail	TS 32
---------	------------------------	------	-------

**Additional technical data**

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

**Dimensions**

Internal thread	M 5	Pitch in mm (P)	12 mm
-----------------	-----	-----------------	-------

**General**

Rail	TS 32	Surface finish	untreated
------	-------	----------------	-----------

**Classifications**

ETIM 6.0	EC000096	ETIM 7.0	EC000096
ETIM 8.0	EC000096	ETIM 9.0	EC000096
ECLASS 9.0	23-11-08-04	ECLASS 9.1	23-11-08-04
ECLASS 10.0	23-11-08-04	ECLASS 11.0	23-11-07-16
ECLASS 12.0	23-11-07-16	ECLASS 13.0	23-11-07-16

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">CAT 1 TERM 16/17 EN</a>