

FM 6/TS35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

General ordering data

Version	Mounting foot on mounting rail, TS 35, M 6
Order No.	0636900000
Type	FM 6/TS35
GTIN (EAN)	4008190174019
Qty.	40 pc(s).

FM 6/TS35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	7 mm	Depth (inches)	0.276 inch
Height	50.2 mm	Height (inches)	1.976 inch
Width	14 mm	Width (inches)	0.551 inch
Net weight	4.62 g		

Material data

Material	Steel, bright finish	Surface finish	nickel-plated
Colour	silver		

System specifications

Version	For the mounting rails	Rail	TS 35
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

Dimensions

Internal thread	M 6	Pitch in mm (P)	14 mm
-----------------	-----	-----------------	-------

General

Rail	TS 35	Surface finish	nickel-plated
------	-------	----------------	---------------

Classifications

ETIM 6.0	EC002625	ETIM 7.0	EC002625
ETIM 8.0	EC002625	ETIM 9.0	EC002625
ECLASS 9.0	27-18-28-07	ECLASS 9.1	23-15-90-90
ECLASS 10.0	27-18-28-07	ECLASS 11.0	27-18-28-07
ECLASS 12.0	27-18-28-07	ECLASS 13.0	27-18-28-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

FM 6/TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

