

## VKSW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

## Általános rendelési adatok

|                |                            |
|----------------|----------------------------|
| Verzió         | Cable duct cutting device  |
| Rendelési szám | <a href="#">1137530000</a> |
| Típus          | VKSW                       |
| GTIN (EAN)     | 4032248919406              |
| Qty.           | 1 Stück                    |

## Műszaki adatok

## Méretetek és tömegek

|             |        |                  |             |
|-------------|--------|------------------|-------------|
| Mélység     | 290 mm | Mélység (coll)   | 11,417 inch |
| Magasság    | 285 mm | Magasság (coll)  | 11,22 inch  |
| Szélesség   | 280 mm | Szélesség (coll) | 11,024 inch |
| Nettó tömeg | 305 g  |                  |             |

## Vágószerszámok

|                    |        |
|--------------------|--------|
| Cutting width max. | 125 mm |
|--------------------|--------|

## Besorolások

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000149    | ETIM 7.0    | EC000149    |
| ETIM 8.0    | EC000149    | ETIM 9.0    | EC000149    |
| ECLASS 9.0  | 21-04-50-03 | ECLASS 9,1  | 21-01-90-90 |
| ECLASS 10.0 | 21-04-50-03 | ECLASS 11.0 | 21-04-50-03 |
| ECLASS 12.0 | 21-04-50-03 | ECLASS 13.0 | 21-04-50-03 |

## Termékek környezetvédelmi megfelelősége

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0 |

## Letöltések

|             |  |
|-------------|--|
| Katalógusok | <a href="#">Catalogues in PDF-format</a> |
| Kiadványok  |  |

## Tartozékok

## Tartozékok/cserealkatrészek



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

## Általános rendelési adatok

|                |                            |             |
|----------------|----------------------------|-------------|
| Típus          | ERME VKSW                  | Verzió      |
| Rendelési szám | <a href="#">1251270000</a> | Pót vágókés |
| GTIN (EAN)     | 4050118042436              |             |
| Qty.           | 1 Stück                    |             |

---

|                |                            |  |
|----------------|----------------------------|--|
| Típus          | SCHUTZPROFIL VKSW          |  |
| Rendelési szám | <a href="#">8007400000</a> |  |
| GTIN (EAN)     | 4050118392548              |  |
| Qty.           | 1 Stück                    |  |