

HDC 10B SBU 2M25G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Base housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25 |
| Order No. | 1787630000 |
| Type | HDC 10B SBU 2M25G |
| GTIN (EAN) | 4032248204977 |
| Qty. | 1 pc(s). |

HDC 10B SBU 2M25G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|-----------------------------|----------|----------------------------|------------|
| Depth | 115.7 mm | Depth (inches) | 4.555 inch |
| Height | 57 mm | Height (inches) | 2.244 inch |
| Width | 53.5 mm | Width (inches) | 2.106 inch |
| Mounting dimension - height | 43 mm | Mounting dimension - width | 82 mm |
| Net weight | 272 g | | |

Temperatures

| | |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

Dimensions

| | | | |
|----------------------|-----------|----------------------|---------|
| Cable entry | w. thread | Height of base B1 | 5 mm |
| Height of housing B | 57 mm | Hole pitch length A2 | 82 mm |
| Total length housing | 73 mm | Width base C1 | 53.5 mm |
| Width housing C | 43 mm | | |

General data

| | | | |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings | No | Housing main material | diecast aluminium |
| Material of locking element | Stainless steel, rust-proof | Protection degree | IP65 (in plugged condition) |
| Surface finish | Powder coating | | |

Version

| | | | |
|------------------------------|----------------------------------|--------------------------------|--------------|
| BG | 4 | Cable entry | w. thread |
| Clamp version | Side-locking clamp | Colour (RAL) | RAL 7035 |
| Design | Standard | Design of housing | Base housing |
| Design of locking system | Side-locking clamp on lower side | Internal thread | M 25 |
| Number of cable entry on top | 0 | Number of cable entry sideways | 2 |
| Sealing | NBR | Size | 4 |
| Size of cable entries | M 25 | Suitable for ModuPlug® | No |
| Top part/bottom part/lid | lower part | Type | Base housing |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000437 | ETIM 7.0 | EC000437 |
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ECLASS 9.0 | 27-44-02-02 | ECLASS 9.1 | 27-44-02-02 |
| ECLASS 10.0 | 27-44-02-02 | ECLASS 11.0 | 27-44-02-02 |
| ECLASS 12.0 | 27-44-02-02 | ECLASS 13.0 | 27-44-02-02 |

| | |
|---------------------|-------------------------|
| Substance | Acetone |
| Chemical resistance | Conditionally resistant |
| Substance | Drilling oil |
| Chemical resistance | Resistant |
| Substance | Diesel |
| Chemical resistance | Resistant |
| Substance | Ethyl alcohol |
| Chemical resistance | Resistant |

Creation date April 26, 2024 7:38:15 AM CEST

HDC 10B SBU 2M25G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

| | |
|---------------------|-------------------------|
| Substance | Transmission oil |
| Chemical resistance | Resistant |
| Substance | Hydraulic oil |
| Chemical resistance | Resistant |
| Substance | Coolant |
| Chemical resistance | Resistant |
| Substance | Petroleum benzine |
| Chemical resistance | Resistant |
| Substance | Sweat |
| Chemical resistance | Resistant |
| Substance | Premium gasoline |
| Chemical resistance | Conditionally resistant |
| Substance | Water |
| Chemical resistance | Resistant |
| Substance | UV |
| Chemical resistance | Unstable |
| Substance | Ozone |
| Chemical resistance | Unstable |

Environmental Product Compliance

| | |
|---------------------|--|
| REACH SVHC | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP | e98b2b24-ba23-41bf-8d19-Odda3647412f |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@17b9c799 de.myview.objectmodel.impl.BlockImpl@5f81a6aa de.myview.objectmodel.impl.BlockImpl@3812d913 de.myview.objectmodel.impl.BlockImpl@1e5a877b de.myview.objectmodel.impl.BlockImpl@47860e26 de.myview.objectmodel.impl.BlockImpl@15e0448a de.myview.objectmodel.impl.BlockImpl@3b14cd64 de.myview.objectmodel.impl.BlockImpl@71bfe422 de.myview.objectmodel.impl.BlockImpl@63f230d de.myview.objectmodel.impl.BlockImpl@116cf354 de.myview.objectmodel.impl.BlockImpl@c0e73f0 de.myview.objectmodel.impl.BlockImpl@21e08a7 de.myview.objectmodel.impl.BlockImpl@7dc664a2 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E92202 |

HDC 10B SBU 2M25G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[Manufacturer's declaration](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20220214 Technical change to HDC housings](#)

[20220214 Technische Änderung bei HDC-Gehäusen](#)

Technical Documentation

[1787630000 HDC 10B SBU 2M25G STP Blatt 1.pdf](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[FL FIELDWIRING EN](#)

HDC 10B SBU 2M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 24D TSBU 1PG29G | Version |
| Order No. | 1654170000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29 |
| GTIN (EAN) | 4008190406998 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TSBU 1PG21G | Version |
| Order No. | 1654090000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190406912 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TSBU 1M20G | Version |
| Order No. | 1787560000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20 |
| GTIN (EAN) | 4032248204908 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TSBU 1M32G | Version |
| Order No. | 1787230000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32 |
| GTIN (EAN) | 4032248204571 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TSBU 1M25G | Version |
| Order No. | 1787550000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204892 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TSBU 1PG16G | Version |
| Order No. | 1654070000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16 |
| GTIN (EAN) | 4008190406899 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TSBU 1PG21G | Version |
| Order No. | 1654150000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190406974 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TSBU 1M25G | Version |
| Order No. | 1787240000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204588 | |
| Qty. | 1 pc(s). | |

HDC 10B SBU 2M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 10B TOBU 1M20G | Version |
| Order No. | 1787600000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20 |
| GTIN (EAN) | 4032248204946 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TOBU 1PG21G | Version |
| Order No. | 1654240000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21 |
| GTIN (EAN) | 4008190407063 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TOBU 2M20G | Version |
| Order No. | 1336600000 | HDC enclosures, Size: 4, Protection degree: IP65, IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 20 |
| GTIN (EAN) | 4050118175257 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TOBU 1M25G | Version |
| Order No. | 1787300000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204649 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TOBU 1PG29G | Version |
| Order No. | 1654320000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29 |
| GTIN (EAN) | 4008190407148 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TOBU 1M25G | Version |
| Order No. | 1787590000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25 |
| GTIN (EAN) | 4032248204939 | |
| Qty. | 1 pc(s). | |
| Type | HDC 10B TOBU 1PG16G | Version |
| Order No. | 1654220000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16 |
| GTIN (EAN) | 4008190407049 | |
| Qty. | 1 pc(s). | |
| Type | HDC 24D TOBU 1M32G | Version |
| Order No. | 1787290000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32 |
| GTIN (EAN) | 4032248204632 | |
| Qty. | 1 pc(s). | |

HDC 10B SBU 2M25G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | HDC 10B DODQ 4B0 | Version |
| Order No. | 1665230000 | HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cover for lower part of housing, Side-locking clamp on lower side, Standard |
| GTIN (EAN) | 4008190421939 | |
| Qty. | 1 pc(s). | |