

IE-PP-V04P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For protecting your devices against dust and dirt.

General ordering data

Version	Plug housing protective cap
Order No.	1963890000
Type	IE-PP-V04P
GTIN (EAN)	4032248646319
Qty.	10 pc(s).

IE-PP-V04P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	46.7 mm	Depth (inches)	1.839 inch
Net weight	10.3 g		

Temperatures

Operating temperature	-40 °C...70
-----------------------	-------------

General data

Colour	black	Housing main material	PA UL 94 V0
Protection degree	IP67	Type of mounting	Indoors only
UL 94 flammability rating	V-0		

General standards

Certificate no. (cULus)	E316369
-------------------------	---------

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ETIM 9.0	EC002314
ECLASS 9.0	27-44-02-08	ECLASS 9.1	27-44-02-08
ECLASS 10.0	27-44-02-08	ECLASS 11.0	27-44-02-08
ECLASS 12.0	27-44-02-08	ECLASS 13.0	27-44-02-08

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Downloads

Approval/Certificate/Document of Conformity	UL Approval GOST Approval
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PP-V04P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

