

**CD-RET 100/120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Version	Cable duct binder
Order No.	<a href="#">2554060000</a>
Type	CD-RET 100/120
GTIN (EAN)	4050118564181
Qty.	250 pc(s).

**CD-RET 100/120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	4 g
------------	-----

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General information**

Channel width	75/100/120	Colour	yellow
Material	Polyamide 6 (PA 6)	Non-tracking	Yes
Operating temperature range	-40...100 °C	UL 94 flammability rating	HB
Usage	For 75/ 100/ 120 mm wiring ducts		

**Classifications**

ETIM 6.0	EC001018	ETIM 7.0	EC001018
ETIM 8.0	EC001018	ETIM 9.0	EC001018
ECLASS 9.0	27-40-07-65	ECLASS 9.1	27-40-07-65
ECLASS 10.0	27-40-07-65	ECLASS 11.0	27-40-07-65
ECLASS 12.0	27-40-07-65	ECLASS 13.0	27-40-07-65

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--