

**M-D-STRIPAX +6 MEHA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

**General ordering data**

Version	Tools, Stripping and cutting tool
Order No.	<a href="#">9003500000</a>
Type	M-D-STRIPAX +6 MEHA
GTIN (EAN)	4008190107109
Qty.	1 pc(s).

**M-D-STRIPAX +6 MEHA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	135 mm	Height (inches)	5.315 inch
Width	82 mm	Width (inches)	3.228 inch
Net weight	106.38 g		

**Technical data**

Description of article	Stripping tool with 6 sets of blades
------------------------	--------------------------------------

**Stripping tools**

Cable type	Conductor with custom insulation	Conductor cross-section, max.	0.82 mm <sup>2</sup>
Conductor cross-section, min.	0.03 mm <sup>2</sup>	Max. conductor diameter	1.3 mm
Min. conductor diameter	0.2 mm	Stripping length, max.	7 mm
Stripping range AWG, max.	18 AWG	Stripping range AWG, min.	32 AWG

**Classifications**

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### M-D-STRIPAX +6 MEHA

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



## M-D-STRIPAX +6 MEHA

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Accessories / replacement parts



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

### General ordering data

Type	MEHA KP GN M-D-SPX	Version
Order No.	<a href="#">9003620000</a>	Accessories, Set of cutters
GTIN (EAN)	4008190130527	
Qty.	1 pc(s).	
Type	MEHA KP BL M-D-SPX	Version
Order No.	<a href="#">9003630000</a>	Accessories, Set of cutters
GTIN (EAN)	4008190094256	
Qty.	1 pc(s).	
Type	MEHA KP WS M-D-SPX	Version
Order No.	<a href="#">9006970000</a>	Accessories, Set of cutters
GTIN (EAN)	4032248363711	
Qty.	1 pc(s).	
Type	MEHA KP SW M-D-SPX	Version
Order No.	<a href="#">9003640000</a>	Accessories, Set of cutters
GTIN (EAN)	4008190020507	
Qty.	1 pc(s).	
Type	MEHA KP GE M-D-SPX	Version
Order No.	<a href="#">9003600000</a>	Accessories, Set of cutters
GTIN (EAN)	4008190140274	
Qty.	1 pc(s).	
Type	MEHA KP RT M-D-SPX	Version
Order No.	<a href="#">9003610000</a>	Accessories, Set of cutters
GTIN (EAN)	4008190058272	
Qty.	1 pc(s).	