

RZ 160**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

up to 1000 V (AC) and 1500 V (DC)
protective insulation acc. to IEC 900. DIN EN 60900

- drop-forged from high-quality special tool steels
- safety handle with ergonomic and non-slip TPE VDE sleeve
- Made from shockproof, heat-and cold-resistant, non-flammable, cadmium-free TPE (thermoplastic elastomer)
- Elastic grip zone and hard core
- Highly-polished surface
- nickel-chromium electro-galvanised coating protects against corrosion

General ordering data

Version	Pliers
Order No.	9046360000
Type	RZ 160
GTIN (EAN)	4032248357666
Qty.	1 pc(s).

RZ 160**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	160 mm	Width (inches)	6.299 inch
Net weight	127 g		

Technical data

Description of article	VDE-insulated round-nose pliers with long jaws
------------------------	--

Pliers

Length of jaws	45 mm	Protective insulation, 1000 V	Yes
Total length	160 mm		

Classifications

ETIM 6.0	EC000834	ETIM 7.0	EC000834
ETIM 8.0	EC000834	ETIM 9.0	EC000834
ECLASS 11.0	21-04-38-21	ECLASS 12.0	21-04-38-21
ECLASS 13.0	21-04-38-21		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Approvals

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Pliers
Catalogues	Catalogues in PDF-format
Brochures	