

QB 25/6.5/11.5 SAKR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 25, Pitch in mm (P): 6.50, Insulated: No, 32 A, grey
Order No.	0134000000
Type	QB 25/6.5/11.5 SAKR
GTIN (EAN)	4008190118945
Qty.	20 pc(s).

QB 25/6.5/11.5 SAKR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	13.24 mm	Depth (inches)	0.521 inch
Height	158.6 mm	Height (inches)	6.244 inch
Width	0.9 mm	Width (inches)	0.035 inch
Net weight	7.852 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
Type of mounting	when screwed in		

Cross-connector

Type	Cross-connector
------	-----------------

Dimensions

Pitch in mm (P)	6.5 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	25
---------------------	-----------------	-----------------	----

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format