

SS M3 D 128-A 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Lock washer, Copper
Order No.	0164400000
Type	SS M3 D 128-A 3
GTIN (EAN)	4008190035914
Qty.	50 pc(s).

SS M3 D 128-A 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Diameter	6.2 mm	Wall thickness, max.	1.2 mm
Net weight	0.1 g		

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Rail
---------------------	-----------------	------------------	------

Dimensions

Diameter	6.2 mm
----------	--------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002345	ETIM 7.0	EC002345
ETIM 8.0	EC002345	ETIM 9.0	EC002345
ECLASS 9.0	23-09-03-06	ECLASS 9.1	23-09-92-90
ECLASS 10.0	23-09-92-90	ECLASS 11.0	23-09-03-06
ECLASS 12.0	23-09-03-09	ECLASS 13.0	23-09-03-09
ECLASS 14.0	23-09-03-09		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	