

**QL 3 SAK70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 180 A, Number of poles: 3, Pitch in mm (P): 14.00, Insulated: No, Width: 58 mm
Order No.	<a href="#">0167000000</a>
Type	QL 3 SAK70
GTIN (EAN)	4008190001018
Qty.	5 pc(s).

**QL 3 SAK70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	4 mm	Depth (inches)	0.157 inch
Height	14 mm	Height (inches)	0.551 inch
Width	58 mm	Width (inches)	2.283 inch
Net weight	25.2 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Cu Zn	Colour	grey
----------	-------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	192 A
Rated current, multi-pole	192 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	14 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	180 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	86596b21-b817-43a9-8e4c-ac00e41b9a24
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

## QL 3 SAK70

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**QL 3 SAK70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Connection sleeves****General ordering data**

Type	VH 30.5/11/5.5 SAK70	Version
Order No.	<a href="#">0345500000</a>	Connecting sleeve (terminal), when screwed in, Width: 11 mm,
GTIN (EAN)	4008190100698	Height: 11 mm, Depth: 30.5 mm, Cu Zn
Qty.	20 pc(s).	

**Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

**General ordering data**

Type	BFSC M5X45	Version
Order No.	<a href="#">0345600000</a>	Mounting screw (Terminal), Steel, Height: 45 mm
GTIN (EAN)	4008190058739	
Qty.	20 pc(s).	

**QL 3 SAK70****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Miscellaneous**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Type	SS M5 D 128-A 5	Version
Order No.	<a href="#">0346100000</a>	Lock washer, Copper
GTIN (EAN)	4008190137199	
Qty.	50 pc(s).	