

**EP 2 SAKG46/35 HP/DBR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	End and partition plate for terminals, End and intermediate plate, 160 mm x 2 mm, dark brown
Order No.	<a href="#">0180700000</a>
Type	EP 2 SAKG46/35 HP/DBR
GTIN (EAN)	4008190099671
Qty.	10 pc(s).

## EP 2 SAKG46/35 HP/DBR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	91 mm	Depth (inches)	3.583 inch
Height	160 mm	Height (inches)	6.299 inch
Width	2 mm	Width (inches)	0.079 inch
Net weight	35.4 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

## Material data

Material	PA 66	Colour	dark brown
UL 94 flammability rating	V-2		

## System specifications

Version	End and intermediate plate
---------	----------------------------

## Additional technical data

Snap-on	No
---------	----

## Dimensions

TS 32 offset	80 mm
--------------	-------

## Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.0	27-14-11-33	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-25-03-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8689236b-1c04-4b82-9d8d-177abb5f9950

## Approvals

ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>