

**AP SAKS1+3 KRG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

AP 019132



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	End plate (terminals), 54 mm x 3 mm, dark beige, yellow
Order No.	<a href="#">0191320000</a>
Type	AP SAKS1+3 KRG
GTIN (EAN)	4008190031688
Qty.	20 pc(s).

**AP SAKS1+3 KRG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	36 mm	Depth (inches)	1.417 inch
Height	54 mm	Height (inches)	2.126 inch
Width	3 mm	Width (inches)	0.118 inch
Net weight	7.4 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

**Material data**

Material	KrG	Colour	dark beige, yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	End plate
---------	-----------

**Additional technical data**

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Classifications**

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.1	27-14-11-33	ECLASS 10.0	27-14-11-33
ECLASS 11.0	27-14-11-33	ECLASS 12.0	27-14-11-33
ECLASS 13.0	27-25-03-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>