

BFSC M2.5X14 SAKD2.5N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Version	Mounting screw (Terminal)
Order No.	0266800000
Type	BFSC M2.5X14 SAKD2.5N
GTIN (EAN)	4008190084899
Qty.	100 pc(s).

BFSC M2.5X14 SAKD2.5N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	14 mm	Height (inches)	0.551 inch
Diameter	3.8 mm	Net weight	0.56 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Colour	beige
--------	-------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Dimensions

Diameter	3.8 mm	Pitch in mm (P)	5.1 mm
----------	--------	-----------------	--------

General

Installation advice	Direct mounting	Number of poles	1
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format