

EP 2/BW SAKG46/32 HP/DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Version	SAK Series, End plate, dark beige, 75.5 mm
Order No.	0271900000
Type	EP 2/BW SAKG46/32 HP/DB
GTIN (EAN)	4008190172497
Qty.	10 pc(s).

EP 2/BW SAKG46/32 HP/DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	90.5 mm	Depth (inches)	3.563 inch
Height	160 mm	Height (inches)	6.299 inch
Width	75.5 mm	Width (inches)	2.972 inch
Net weight	51.2 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	Plastic	Colour	dark beige
UL 94 flammability rating	V-2		

System specifications

Version	with end bracket
---------	------------------

Additional technical data

Explosion-tested version	No	Interlock	for screw fixing
Type of fixing	when screwed in		

Dimensions

Pitch in mm (P)	160 mm	TS 32 offset	80 mm
-----------------	--------	--------------	-------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.0	27-14-11-33	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-25-03-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8689236b-1c04-4b82-9d8d-177abb5f9950

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format