

**SH 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Busbar support             |
| Order No.  | <a href="#">0299860000</a> |
| Type       | SH 1                       |
| GTIN (EAN) | 4008190135133              |
| Qty.       | 20 pc(s).                  |

## SH 1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 24 mm   | Depth (inches)  | 0.945 inch |
| Height     | 24.5 mm | Height (inches) | 0.965 inch |
| Width      | 26 mm   | Width (inches)  | 1.024 inch |
| Net weight | 2 g     |                 |            |

## Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

## Material data

|          |              |                           |            |
|----------|--------------|---------------------------|------------|
| Material | Polyamide 66 | Surface finish            | all others |
| Colour   | beige        | UL 94 flammability rating | V-2        |

## Additional technical data

|                     |                 |                  |                 |
|---------------------|-----------------|------------------|-----------------|
| Installation advice | Direct mounting | Type of mounting | when screwed in |
|---------------------|-----------------|------------------|-----------------|

## Conductors for clamping (rated connection)

|                    |               |
|--------------------|---------------|
| Type of connection | Miscellaneous |
|--------------------|---------------|

## General

|                     |                 |                                   |        |
|---------------------|-----------------|-----------------------------------|--------|
| Installation advice | Direct mounting | Operating temperature range, max. | 100 °C |
| Surface finish      | all others      |                                   |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001166    | ETIM 7.0    | EC001166    |
| ETIM 8.0    | EC001166    | ETIM 9.0    | EC001166    |
| ECLASS 9.0  | 27-40-06-07 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-40-06-07 | ECLASS 11.0 | 27-40-06-07 |
| ECLASS 12.0 | 27-40-06-07 | ECLASS 13.0 | 27-40-06-07 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |  |
|--------------------|--|
| Engineering Data   | <a href="#">CAD data – 02961_SH_1_DXF.dxf</a><br><a href="#">CAD data – STEP</a> |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a>                                  |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>   |
| Brochures          |  |