

**KISC M3X20.5/10 EK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Clamping yoke, Mounting screw, Steel
Order No.	<a href="#">0303000000</a>
Type	KISC M3X20.5/10 EK4
GTIN (EAN)	4008190163686
Qty.	100 pc(s).

**KISC M3X20.5/10 EK4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	4.8 mm	Depth (inches)	0.189 inch
Height	20 mm	Height (inches)	0.787 inch
Width	4.8 mm	Width (inches)	0.189 inch
Diameter	3 mm	Net weight	1.16 g

**Material data**

Material	Steel	Surface finish	Miscellaneous
Colour	silver		

**System specifications**

Version	for busbars
---------	-------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

**Dimensions**

Diameter	3 mm	Metric size of the thread, external	3 mm
----------	------	-------------------------------------	------

**General**

Installation advice	Direct mounting	Surface finish	Miscellaneous
---------------------	-----------------	----------------	---------------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90
ECLASS 14.0	27-25-03-90		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>