

**QL 10 SAK2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, 32 A, grey
Order No.	<a href="#">0338100000</a>
Type	QL 10 SAK2.5
GTIN (EAN)	4008190189426
Qty.	20 pc(s).

**QL 10 SAK2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	0.6 mm	Depth (inches)	0.024 inch
Height	6 mm	Height (inches)	0.236 inch
Width	60.6 mm	Width (inches)	2.386 inch
Net weight	1.55 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Copper	Colour	grey
----------	--------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	10	Rated current, 2-pole	41 A
Rated current, multi-pole	41 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	6 mm
-----------------	------

**General**

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

**Rating data**

Rated current	32 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Approvals**

ROHS	Conform
------	---------

### QL 10 SAK2.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

**QL 10 SAK2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Connection sleeves****General ordering data**

Type	VH 8/4.9/3.3	Version
Order No.	<a href="#">0266700000</a>	Connecting sleeve (terminal), Height: 4.9 mm, Width: 4.9 mm, Depth:
GTIN (EAN)	4008190152031	8 mm, Copper
Qty.	100 pc(s).	

**Screws**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

**General ordering data**

Type	KISC M3X15/6 SAK2.5	Version
Order No.	<a href="#">0359000000</a>	Clamping yoke, Mounting screw, Steel
GTIN (EAN)	4008190061548	
Qty.	100 pc(s).	