

**MF TBF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The enclosures of the TBF series are made of extremely tough glass fibre-reinforced polyester. These enclosures are ideal for applications that call for low weight coupled with high shock resistance. The weather-resistant TBF enclosures are designed for a wide range of applications. Together with their comprehensive range of accessories, they provide universal solutions for accommodating built-in items such as regulators, measuring instruments, valves and other equipment.

**Features:**

- 9 sizes in 2 versions, with grey and transparent lids
- Cover with nylon screws
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails and mounting plates
- Comprehensive accessories
- Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

|            |   |
|------------|---|
| Version    | TBF (polyester empty enclosure), Mounting foot, Fixing lugs, Height: 72.5 mm, Width: 24 mm, Depth: 12 mm, Material: Polyamide, Deep black |
| Order No.  | <a href="#">0360800000</a>  |
| Type       | MF TBF  |
| GTIN (EAN) | 4008190108595   |
| Qty.       | 1 pc(s).  |

**MF TBF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 12 mm   | Depth (inches)  | 0.472 inch |
| Height     | 72.5 mm | Height (inches) | 2.854 inch |
| Width      | 24 mm   | Width (inches)  | 0.945 inch |
| Net weight | 69 g    |                 |            |

**General information**

|          |           |                |                 |
|----------|-----------|----------------|-----------------|
| Material | Polyamide | Type of fixing | when screwed in |
|----------|-----------|----------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002625    | ETIM 7.0    | EC002625    |
| ETIM 8.0    | EC002625    | ETIM 9.0    | EC002625    |
| ECLASS 9.0  | 27-18-28-07 | ECLASS 9.1  | 27-18-92-90 |
| ECLASS 10.0 | 27-18-28-07 | ECLASS 11.0 | 27-18-28-07 |
| ECLASS 12.0 | 27-18-28-07 | ECLASS 13.0 | 27-18-28-07 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
| Brochures  |  |