

**H1,0/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

**General ordering data**

|            |  |
|------------|--|
| Version    | Wire-end ferrule, Standard, 6 mm, 6 mm, No |
| Order No.  | <a href="#">0372600000</a>                 |
| Type       | H1,0/6                                     |
| GTIN (EAN) | 4008190180263                              |
| Qty.       | 1,000 pc(s).                               |
| Packaging  | loose                                      |

**H1,0/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 0.04 g |
|------------|--------|

**Technical data**

|                        |   |         |          |
|------------------------|---|---------|----------|
| Description of article | Wire end ferrule without plastic collar | Version | Standard |
|------------------------|---|---------|----------|

**Wire-end ferrules**

|   |        |                             |                   |
|---|--------|-----------------------------|-------------------|
| Collar diameter (D2)                    | 2.5 mm | Conductor cross-section     | 1 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 1.4 mm | Contact surface length (L2) | 6 mm              |
| L1 in mm                                | 6 mm   | Stripping length            | 6 mm              |
| Wire connection cross section AWG, max. | AWG 17 |                             |                   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000005    | ETIM 7.0    | EC000005    |
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ECLASS 9.0  | 27-40-02-01 | ECLASS 9.1  | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

**Approvals**

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate no. (cULus) | E499744    |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">Zuken E3.S</a>               |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**H1,0/6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

