

IH 4.8 DB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

With insulating sleeve for cable lug, an increase of the rated voltage within the application is possible.

General ordering data

Version	W-Series, Insulating sleeve
Order No.	0386160000
Type	IH 4.8 DB
GTIN (EAN)	4008190141004
Qty.	100 pc(s).

IH 4.8 DB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	22 mm	Height (inches)	0.866 inch
Width	7 mm	Width (inches)	0.276 inch
Net weight	0.34 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-50 °C...
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	dark beige
UL 94 flammability rating	V-2		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

UL rating data

Certificate No. (UR)	E60693
----------------------	--------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format