

**STB 35 IH/GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

**General ordering data**

Version	Socket (terminal), Plug-in depth: 8 mm, Depth: 37.5 mm
Order No.	<a href="#">0388900000</a>
Type	STB 35 IH/GN
GTIN (EAN)	4008190010409
Qty.	50 pc(s).

**STB 35 IH/GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	37.5 mm	Depth (inches)	1.476 inch
Width	7.2 mm	Width (inches)	0.283 inch
Net weight	2.18 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	PA 66	Colour	green
UL 94 flammability rating	V-2		

**System specifications**

Version	For the mounting rails
---------	------------------------

**Additional technical data**

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

**Dimensions**

Plug-in depth	8 mm
---------------	------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	