

**STB 35 IH/VI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

**General ordering data**

|            |  |
|------------|--|
| Version    | Socket (terminal), Plug-in depth: 8 mm, Depth: 37.5 mm |
| Order No.  | <a href="#">0389100000</a>                             |
| Type       | STB 35 IH/VI   |
| GTIN (EAN) | 4008190137755  |
| Qty.       | 50 pc(s).  |

**STB 35 IH/VI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                |            |
|------------|---------|----------------|------------|
| Depth      | 37.5 mm | Depth (inches) | 1.476 inch |
| Width      | 7.2     | Width (inches) | 0.283 inch |
| Net weight | 2.36 g  |                |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | PA 66 | Colour | violet |
| UL 94 flammability rating | V-2   |        |        |

**System specifications**

|         |                        |
|---------|------------------------|
| Version | For the mounting rails |
|---------|------------------------|

**Additional technical data**

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in | Type of mounting    | when screwed in |

**Dimensions**

|               |      |
|---------------|------|
| Plug-in depth | 8 mm |
|---------------|------|

**General**

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ECLASS 9.0  | 27-14-11-92 | ECLASS 9.1  | 27-14-11-92 |
| ECLASS 10.0 | 27-14-11-92 | ECLASS 11.0 | 27-14-11-92 |
| ECLASS 12.0 | 27-14-11-92 | ECLASS 13.0 | 27-25-03-90 |
| ECLASS 14.0 | 27-25-03-90 |             |             |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | dce63e23-eea1-4eaa-9071-1c98fc8fa2ea |
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### STB 35 IH/VI

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |