

**Q 10 SAK10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 57 A, Number of poles: 10, Pitch in mm (P): 9.90, Insulated: No, Width: 96.1 mm
Order No.	<a href="#">0457400000</a>
Type	Q 10 SAK10
GTIN (EAN)	4008190016166
Qty.	20 pc(s).

**Q 10 SAK10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	96.1 mm	Width (inches)	3.783 inch
Net weight	28.65 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	CuSn	Colour	grey
----------	------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	10	Rated current, 2-pole	57 A
Rated current, multi-pole	57 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	9.9 mm
-----------------	--------

**General**

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

**Rating data**

Rated current	57 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Q 10 SAK10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>