

IK 4 GG ZB4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

With our accessories for the bus bar taps, you can quickly and easily insulate the tap terminals and visualize the potential through the color coding.

General ordering data

Version	Cover hood (terminal), Polyamide 66
Order No.	0475460000
Type	IK 4 GG ZB4
GTIN (EAN)	4008190065348
Qty.	50 pc(s).

IK 4 GG ZB4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	14.5 mm	Depth (inches)	0.571 inch
Height	19 mm	Height (inches)	0.748 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	0.96 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Insulating material	PA
Colour	silver	UL 94 flammability rating	V-2

System specifications

Version	for busbar 10 x 3 mm
---------	----------------------

Additional technical data

Installation advice	Busbar
---------------------	--------

Dimensions

TS 35 offset	39 mm
--------------	-------

General

Installation advice	Busbar	Operating temperature range, max.	100 °C
---------------------	--------	-----------------------------------	--------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format