

**IK 16/ZB16 GG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

With our accessories for the bus bar taps, you can quickly and easily insulate the tap terminals and visualize the potential through the color coding.

**General ordering data**

Version	Cover hood (terminal), Polyamide 66
Order No.	<a href="#">0502960000</a>
Type	IK 16/ZB16 GG
GTIN (EAN)	4008190113438
Qty.	50 pc(s).

**IK 16/ZB16 GG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	20 mm	Depth (inches)	0.787 inch
Height	19 mm	Height (inches)	0.748 inch
Width	9 mm	Width (inches)	0.354 inch
Net weight	1.18 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Polyamide 66	Insulating material	PA
Colour	silver	UL 94 flammability rating	V-2

**System specifications**

Version	for busbar 10 x 3 mm
---------	----------------------

**Conductors for clamping (rated connection)**

Number of connections	1
-----------------------	---

**Dimensions**

TS 35 offset	39 mm
--------------	-------

**General**

Operating temperature range, max.	100 °C
-----------------------------------	--------

**Rating data**

Pollution severity	3
--------------------	---

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>