

MB M3/M5 CRM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Mounting feet are used to mount components that cannot be snapped directly on a DIN rail.

General ordering data

Version	Sliding nut, M 5
Order No.	0503500000
Type	MB M3/M5 CRM
GTIN (EAN)	4008190182083
Qty.	20 pc(s).

MB M3/M5 CRM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	14 mm	Depth (inches)	0.551 inch
Height	25 mm	Height (inches)	0.984 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	3.55 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Surface finish	untreated
Colour	Cream	UL 94 flammability rating	V-2

System specifications

Version	For the mounting rails	Rail	TS 32
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

Dimensions

Internal thread	M 5	Pitch in mm (P)	12 mm
-----------------	-----	-----------------	-------

General

Rail	TS 32	Surface finish	untreated
------	-------	----------------	-----------

Classifications

ETIM 6.0	EC000096	ETIM 7.0	EC000096
ETIM 8.0	EC000096	ETIM 9.0	EC000096
ECLASS 9.0	23-11-08-04	ECLASS 9.1	23-11-08-04
ECLASS 10.0	23-11-08-04	ECLASS 11.0	23-11-07-16
ECLASS 12.0	23-11-07-16	ECLASS 13.0	23-11-07-16

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	CAT 1 TERM 16/17 EN

MB M3/M5 CRM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

