

**CLI MH 70 HSTR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

**Advantages:**

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

**General ordering data**

Version	CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black
Order No.	<a href="#">0524400000</a>
Type	CLI MH 70 HSTR
GTIN (EAN)	4008190075057
Qty.	100 pc(s).

**CLI MH 70 HSTR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	70 mm	Height (inches)	2.756 inch
Width	11.3 mm	Width (inches)	0.445 inch
Net weight	0.81 g		

**Temperatures**

Operating temperature range	-30...100 °C
-----------------------------	--------------

**General data**

Colour	black	
Material	Polyamide 66	
Material colour according to resistance code	0	
Number of markers per combination	1 Component part = Accessories	
Number of markers per packaging unit	Form of supply	Component part
Operating temperature range	-30... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-30 °C	
Recommended industries	Process, Machinery	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	halogen-free	
Width	11.3 mm	

**Conductor and cable markers**

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 500 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### CLI MH 70 HSTR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use

