

**QB 75/6.2/9/WI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 75, Pitch in mm (P): 6.00, Insulated: No, Width: 0.8 mm
Order No.	<a href="#">0526400000</a>
Type	QB 75/6.2/9/WI
GTIN (EAN)	4008190099923
Qty.	10 pc(s).

## QB 75/6.2/9/WI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	461.3 mm	Height (inches)	18.161 inch
Width	0.8 mm	Width (inches)	0.031 inch
Net weight	25.02 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper	Colour	grey
----------	--------	--------	------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	75	Rated current, 2-pole	27 A
Rated current, multi-pole	27 A	Type	Cross-connector

## Dimensions

Pitch in mm (P)	6 mm
-----------------	------

## General

Installation advice	Direct mounting	Number of poles	75
---------------------	-----------------	-----------------	----

## Rating data

Rated current	27 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**QB 75/6.2/9/WI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**QB 75/6.2/9/WI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Insulation profiles****General ordering data**

Type	ISPF QB75 BL	Version
Order No.	<a href="#">0526780000</a>	Insulation profile, Plastic, blue
GTIN (EAN)	4008190093105	
Qty.	10 pc(s).	
Type	ISPF QB75 SW	Version
Order No.	<a href="#">0526700000</a>	Insulation profile, Plastic, black
GTIN (EAN)	4008190093723	
Qty.	10 pc(s).	
Type	ISPF QB75 RT	Version
Order No.	<a href="#">0526760000</a>	Insulation profile, Plastic, red
GTIN (EAN)	4008190157821	
Qty.	10 pc(s).	