

QB 75/6.2/15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 75, Pitch in mm (P): 6.00, Insulated: No, Width: 0.8 mm
Order No.	0535200000
Type	QB 75/6.2/15
GTIN (EAN)	4008190179168
Qty.	10 pc(s).

QB 75/6.2/15

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	461.3 mm	Height (inches)	18.161 inch
Width	0.8 mm	Width (inches)	0.031 inch
Net weight	26.26 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	75	Rated current, 2-pole	27 A
Rated current, multi-pole	27 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	6 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	75
---------------------	-----------------	-----------------	----

Rating data

Rated current	27 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

QB 75/6.2/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

QB 75/6.2/15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Insulation profiles****General ordering data**

Type	ISPF QB75 RT	Version
Order No.	0526760000	Insulation profile, Plastic, red
GTIN (EAN)	4008190157821	
Qty.	10 pc(s).	
Type	ISPF QB75 BL	Version
Order No.	0526780000	Insulation profile, Plastic, blue
GTIN (EAN)	4008190093105	
Qty.	10 pc(s).	
Type	ISPF QB75 SW	Version
Order No.	0526700000	Insulation profile, Plastic, black
GTIN (EAN)	4008190093723	
Qty.	10 pc(s).	