

H0,75/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 10 mm, No
Order No.	0542500000
Type	H0,75/10
GTIN (EAN)	4008190037482
Qty.	1,000 pc(s).
Packaging	loose

H0,75/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.06 g
------------	--------

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Collar diameter (D2)	2.3 mm	Conductor cross-section	0.75 mm ²
Contact surface diameter (D1)	1.2 mm	Contact surface length (L2)	10 mm
L1 in mm	10 mm	Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01
ECLASS 14.0	27-40-02-01		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

H0,75/10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

