

**ISPF QB58 RT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	Insulation profile, PVC, red
Order No.	<a href="#">0546040000</a>
Type	ISPF QB58 RT
GTIN (EAN)	4008190497941
Qty.	10 pc(s).

## ISPF QB58 RT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5.7 mm	Depth (inches)	0.224 inch
Height	465 mm	Height (inches)	18.307 inch
Width	2.5 mm	Width (inches)	0.098 inch
Net weight	6.08 g		

## Material data

Material	PVC	Colour	red
UL 94 flammability rating	V-0		

## System specifications

Version	Cover profile
---------	---------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged	Type of mounting	Plugged

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

## Approvals

ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>