

CLI RS 4 MDCLI C1+02**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Version	CableLine, Mounting mandrel
Order No.	0559300000
Type	CLI RS 4 MDCLI C1+02
GTIN (EAN)	4008190112400
Qty.	1 pc(s).

CLI RS 4 MDCLI C1+02

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	4 mm	Depth (inches)	0.157 inch
Height	100 mm	Height (inches)	3.937 inch
Width	4 mm	Width (inches)	0.157 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	0.027 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	silver	Halogen	Yes
Length	100 mm	Material	Steel
Operating temperature range	-30...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Printed characters	Numbers
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	MultiPack
Width	4 mm		

Conductor and cable markers

Conductor O.D.	2.5 - 4.5 mm	Conductor O.D., max.	4.5 mm
Conductor O.D., min.	2.5 mm	Conductor cross-section, max.	3.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Cross-section for connected wire	1.5 - 3.5 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	70267faf-4457-48b8-92bf-2799db2a9227

Downloads

Catalogues	Catalogues in PDF-format
------------	--