

**CLI RH 20-10 CLI R 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

**General ordering data**

Version	CableLine, Mounting mandrel holder
Order No.	<a href="#">0563600000</a>
Type	CLI RH 20-10 CLI R 10
GTIN (EAN)	4008190018436
Qty.	1 pc(s).

**CLI RH 20-10 CLI R 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	28 mm	Depth (inches)	1.102 inch
Height	55 mm	Height (inches)	2.165 inch
Width	55 mm	Width (inches)	2.165 inch
Net weight	44 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Colour	blue	Halogen	Yes
Material	Polyamide	Material colour according to resistance code	6
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Recommended industries	Process, Machinery
UL 94 flammability rating	V-0	Width	55 mm

**Conductor and cable markers**

Halogen	Yes
---------	-----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### CLI RH 20-10 CLI R 10

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use

