

G 25/0.80A/M GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x25 mm in sizes from 250 mA to 6.3 A.

General ordering data

Version	Miniature fuse, medium time-lag, 0.8 A, G-Si. 5 x 25
Order No.	0646400000
Type	G 25/0.80A/M GR
GTIN (EAN)	4008190060794
Qty.	10 pc(s).

G 25/0.80A/M GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	25 mm	Height (inches)	0.984 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	1.2 g		

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Cartridge fuse	G-Si. 5 x 25	Characteristics	medium time-lag
Colour	Light Grey	Colour of the indicator	grey
Current	0.8 A	Melting integral	1.6 A²s
Optical function display	Yes	Power output (@ 1.5 In)	0.2 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	400 mV		

Rating data

Rated voltage	250 V	Rated current	0.8 A
---------------	-------	---------------	-------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ECLASS 9.0	27-14-20-01	ECLASS 9.1	27-14-20-01
ECLASS 10.0	27-14-20-01	ECLASS 11.0	27-14-20-01
ECLASS 12.0	27-14-20-01	ECLASS 13.0	27-14-20-01

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	