

CLI O 30-3 GE/SW ET MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm² to max. 4.0 mm². The shape and design guarantee secure and permanent attachment of the individually combinable markers.

Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

General ordering data

Version	CableLine, Conductor and cable markers, 4 - 5 mm, 3 x 6 mm, yellow
Order No.	0648201746
Type	CLI O 30-3 GE/SW ET MP
GTIN (EAN)	4032248541492
Qty.	200 pc(s).

CLI O 30-3 GE/SW ET MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6 mm	Depth (inches)	0.236 inch
Height	3 mm	Height (inches)	0.118 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	0.055 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Material colour according to resistance code	4	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Symbols
Printing	ET	Printing method	hot-embossing
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	MultiPack
Width	6 mm		

Conductor and cable markers

Conductor O.D.	4 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	4 mm	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	3 mm ²	Cross-section for connected wire	3 - 4 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CLI O 30-3 GE/SW ET MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration