

**SKMU M20 MS SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|                     |  |
|---------------------|--|
| Version             | SKMU MS (brass locknut), Locknut, M 20, 4 mm, Brass            |
| Order No.           | <a href="#">0930640002</a>                                     |
| Type                | SKMU M20 MS SC   |
| GTIN (EAN)          | 4032248849826  |
| Qty.                | 50 pc(s).  |
| Delivery status     | <b>This article will no longer be available in the future.</b> |
| Available until     | 2024-08-31   |
| Alternative product | <a href="#">1737000000</a>                                     |

**SKMU M20 MS SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 3 mm   | Height (inches) | 0.118 inch |
| Net weight | 5.64 g |                 |            |

**General information**

|                 |       |                  |        |
|-----------------|-------|------------------|--------|
| AF size 1       | 24 mm | Cable glands     | M 20   |
| External thread | M 20  | Halogen          | No     |
| Internal thread | M 20  | Length of thread | 4 mm   |
| Material        | Brass | Pitch of thread  | 1.5 mm |
| Thickness       | 4 mm  |                  |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000940    | ETIM 7.0    | EC000940    |
| ETIM 8.0    | EC000940    | ETIM 9.0    | EC000940    |
| ECLASS 9.0  | 27-14-44-24 | ECLASS 9.1  | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |
| ECLASS 14.0 | 27-14-08-05 |             |             |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

### SKMU M20 MS SC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

