

EA-RING MS/M50 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EA (earthing rings), Earthing ring, Miscellaneous, M 50, Brass
Order No.	0930710006
Type	EA-RING MS/M50 SC
GTIN (EAN)	4032248976218
Qty.	10 pc(s).

EA-RING MS/M50 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	111 mm	Height (inches)	4.37 inch
Length	111 mm	Length (inches)	4.37 inch
Net weight	36 g		

General information

Cable glands	M 50	External thread	M 50
Gap, internal dimension B	58.1 mm	Inside diameter D2	13.5 mm
Material	Brass	O.D.	65.2 mm
Thickness	1.5 mm	Width, outer dimension C	41.3 mm

Classifications

ETIM 6.0	EC002317	ETIM 7.0	EC002317
ETIM 8.0	EC002317	ETIM 9.0	EC002317
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

EA-RING MS/M50 SC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

