

WQL 5 WF10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

| | |
|------------|--|
| Version | Bolt-type screw terminals, Cross-connector, Number of poles: 5 |
| Order No. | 1016870000 |
| Type | WQL 5 WF10 |
| GTIN (EAN) | 4032248726530 |
| Qty. | 5 pc(s). |

WQL 5 WF10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 4 mm | Depth (inches) | 0.157 inch |
| Height | 163.2 mm | Height (inches) | 6.425 inch |
| Width | 25 mm | Width (inches) | 0.984 inch |
| Net weight | 127.8 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|---------------|--------|------|
| Material | Copper - zinc | Colour | grey |
|----------|---------------|--------|------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

Dimensions

| | | | |
|-----------------|---------|--------------|-------|
| Pitch in mm (P) | 33.8 mm | TS 35 offset | 36 mm |
|-----------------|---------|--------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 5 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|-------|
| Rated current | 265 A |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |