

**SFC 3/12 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

**Advantages:**

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the heights of 12 mm, 21 mm and 30 mm

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	SlimFix Clip, Conductor and cable markers, 3.5 - 7 mm, 12 x 12.5 mm, To customer specification
Order No.	<a href="#">1025550000</a>
Type	SFC 3/12 MC SDR
GTIN (EAN)	4032248746736
Qty.	16 pc(s).
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

**SFC 3/12 MC SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	11.3 mm	Depth (inches)	0.445 inch
Height	12 mm	Height (inches)	0.472 inch
Width	12.5 mm	Width (inches)	0.492 inch
Net weight	0.87 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	
Colour	To customer specification	
Colour of printing	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Orientation of print	horizontal	
Printed characters	Based on customer requirements (Please send M-Print PRO file)	
Printing method	MC Laser	
Size of labelling field	12 x 5 mm	
Type of printing	To customer specification	
UL 94 flammability rating	V-2	
Width	12.5 mm	

**Conductor and cable markers**

Conductor O.D.	3.5 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	3.5 mm	Conductor cross-section, max.	10 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Cross-section for connected wire	4 - 10 mm <sup>2</sup>
Halogen	No		

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

### SFC 3/12 MC SDR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Catalogues

[Catalogues in PDF-format](#)

Brochures