

WQV 35/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), when screwed in, yellow, 138 A, Number of poles: 2, Pitch in mm (P): 16.00, Insulated: Yes, Width: 9.85 mm |
| Order No. | 1053060000 |
| Type | WQV 35/2 |
| GTIN (EAN) | 4008190097349 |
| Qty. | 50 pc(s). |

WQV 35/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 28 mm | Depth (inches) | 1.102 inch |
| Height | 28 mm | Height (inches) | 1.102 inch |
| Width | 9.85 mm | Width (inches) | 0.388 inch |
| Net weight | 13.02 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

Cross-connector

| | | | |
|-------------------------------------|-----------------|--|--------------|
| Number of cross-connected terminals | 2 | Rated current, 2-pole | 125 A |
| Rated current, multi-pole | 135 A | Tightening torque range for fixing screw | 1.2...2.4 Nm |
| Type | Cross-connector | | |

Dimensions

| | | | |
|-----------------|-------|--------------|-------|
| Pitch in mm (P) | 16 mm | TS 35 offset | 28 mm |
|-----------------|-------|--------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 2 |
|---------------------|-----------------|-----------------|---|

Rating data

| | | | |
|---------------|-------|---------------|-------|
| Rated voltage | 400 V | Rated current | 138 A |
|---------------|-------|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

WQV 35/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Confirmation of Standards EN 45545-2_2020-10 |
|---|--|

| | |
|------------------|---------------------------------|
| Engineering Data | CAD data – STEP |
|------------------|---------------------------------|

| | |
|------------------|----------------------------|
| Engineering Data | Zuken E3.S |
|------------------|----------------------------|

| | |
|--------------------|--|
| User Documentation | Beipackzettel_WQV.pdf StorageConditionsTerminalBlocks |
|--------------------|--|

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

| | |
|-----------|--|
| Brochures | |
|-----------|--|