

**CB-R 250/7,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

**General ordering data**

Version	Cable ties, 7.5 x 250 mm, Polyamide 66, 220 N
Order No.	<a href="#">1059220000</a>
Type	CB-R 250/7,5 NC
GTIN (EAN)	4032248806164
Qty.	100 pc(s).

## CB-R 250/7,5 NC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	250 mm	Height (inches)	9.842 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	2.58 g		

## Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

## Installation materials

Bundle diameter, max.	65 mm	Bundle diameter, min.	3 mm
Cable diameter, max.	70 mm	For re-opening	Yes
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

## Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

[DE PI830000 160627 001](#)

Catalogues

[Catalogues in PDF-format](#)

## CB-R 250/7,5 NC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Drawing

