

THM GEW 20/8 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers.

Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Version	THM, Device markers, 8 x 20 mm, white
Order No.	1059870000
Type	THM GEW 20/8 WS
GTIN (EAN)	4032248808298
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM GEW 20/8 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	8 mm	Height (inches)	0.315 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	692 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Natural rubber adhesive		
Approval acc. to UL 969	No		
Colour	white		
Halogen	No		
Material	Cotton fabric		
Material colour according to resistance code	9		
Number of markers per combination	1 Label reel = Device markers		
Number of markers per packaging unit	Form of supply	Label reel	
Number per roll	10,000		
Number per sheet	10,000		
Operating temperature range	-29...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-29 °C		
Printing method	Thermal transfer		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	20 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

THM GEW 20/8 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Drawings



THM GEW 20/8 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

THM GEW 20/8 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

