

WQV 35-2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****General ordering data**

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, yellow, 41 A, Number of poles: 3, Pitch in mm (P): 16.00, Insulated: Yes, Width: 13 mm |
| Order No. | 1064100000 |
| Type | WQV 35-2.5 |
| GTIN (EAN) | 4008190142285 |
| Qty. | 10 pc(s). |

WQV 35-2.5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 41.5 mm | Depth (inches) | 1.634 inch |
| Height | 21 mm | Height (inches) | 0.827 inch |
| Width | 13 mm | Width (inches) | 0.512 inch |
| Net weight | 10.721 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
|---------------------|-----------------|----------------|-----------------|

Conductors for clamping (rated connection)

| | | | |
|-------------------------|--------|-------------------------|--------|
| Tightening torque, max. | 0.8 Nm | Tightening torque, min. | 0.4 Nm |
|-------------------------|--------|-------------------------|--------|

Cross-connector

| | | | |
|-------------------------------------|-----------------|---------------------------|------|
| Number of cross-connected terminals | 2 | Rated current, multi-pole | 24 A |
| Type | Cross-connector | | |

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 16 mm |
|-----------------|-------|

General

| | | | |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 3 |
|---------------------|-----------------|-----------------|---|

Rating data

| | |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ECLASS 9.0 | 27-14-11-40 | ECLASS 9.1 | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |
| ECLASS 14.0 | 27-25-03-03 | | |

WQV 35-2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC

/

RoHS Compliance Status

Compliant without exemption

Approvals

ROHS

Conform

DownloadsApproval/Certificate/Document of Con-
formity[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel_WQV16-2.5.pdf](#)
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures