

WQL 3 WFF70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 3
Order No.	1065500000
Type	WQL 3 WFF70
GTIN (EAN)	4008190174811
Qty.	5 pc(s).

WQL 3 WFF70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	89 mm	Height (inches)	3.504 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	41.61 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	192 A
Rated current, multi-pole	232 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	32 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Rating data

Rated current	192 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Creation date June 4, 2024 9:55:59 PM CEST